



Powering Business Worldwide

pe.eaton.com

FERRUPS UPS

FB000AA0A0A0A0A

UPC:790341042042

Dimensions:

- **Height:** 12 IN
- **Length:** 21.25 IN
- **Width:** 10 IN

Weight:62 LB

Warranties:

- 2 year

Specifications:

- **Battery Type:** Internal sealed/gas recombinant/lead-acid battery
- **Efficiency:** 86% efficiency
- **Humidity:** 5 to 95% non-condensing
- **Input:** Hardwired
- **Operating Temperature:** 0° to 40°C
- **User Interface:** On/off switch, alarm switch, 5 front indicator lights
- **Volt Ampere Rating:** 700000 KVA
- **Cable Type:** Communication cable
- **Color:** Beige with blue highlights
- **Configuration:** Tower
- **Runtime:** 11 min full load, 31 min half load
- **Serial Interface:** RS-232 serial port, DB25, plus contact closures
- **Software:** LanSafe, PowerVision, Foreseer
- **Wattage:** 500W

Supporting documents:

- [Eaton FERRUPS UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - FB000AA0A0A0A0A](#)

Certifications:



- CSA Certified
- ANSI/IEEE Std C62.41
- ANSI/IEEE Std C62.45
- IEC 801-4
- IEC 801-5
- UL Listed
- FCC Cat. A
- IEC 801-2

Product compliance: No Data

© 2016 Eaton. All rights reserved.