



Powering Business Worldwide

pe.eaton.com

Receptacle for E50 Heavy Duty Limit Switch

E50RBS12

UPC:782113322193

Dimensions:

- **Height:** 2.92 IN
- **Length:** 1.54 IN
- **Width:** 1.06 IN

Weight:1.9937 LB

Notes:The wire colors referenced on the diagram are those internal to the switch itself. Epoxy filled receptacle with prewired 16 gauge; yellow jacketed; type SOOW-A cable. Cable enters through hole threaded for conduit

Warranties:

- 1 year

Specifications:

- **Connection:** 12 Ft. (3.7m) Cable
- **Cable Type:** SOOW-A
- **Cord Length:** 144 FT
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Operating Temperature:** -40° to 221°F (-40° to 105°C)

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50RBS12](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance:

- CE Marked



