



Powering Business Worldwide

pe.eaton.com

30.5 mm, Class I Division 2 Assembled Control Station

10250T7011S

UPC:782114518564

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Actuator:** Selector switch, knob
- **Actuator Color:** Black
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Stainless steel
- **Legend:** HAND/OFF/AUTO
- **Number Of Elements:** 1
- **Number Of Positions:** Three-position
- **Operating Mode:** Maintained
- **Rating:** NEMA 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T7011S](#)

Certifications: No Data

Product compliance: No Data

