



Powering Business Worldwide

pe.eaton.com

Type PB Tri-Pac Thermal-Magnetic Current Limiter

1600PBPR30

UPC:786679759851

Dimensions:

- **Height:** 4.75 IN
- **Length:** 4.75 IN
- **Width:** 4 IN

Weight:3.44 LB

Notes:Supplied as standard on 1200-1600A ratings. Optional on lower ratings where a higher “cross-over point” is desired. (Replaces limiter 4000PBR30 formerly supplied on 1200-1400A ratings, and 5000PBPR42 supplied on 1600A ratings.)

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 1200-1600A

Supporting documents:

- [Miniature and Molded Case Circuit Breakers](#)
- [Eaton Specification Sheet - 1600PBPR30](#)

Certifications:

- UL 489

Product compliance: No Data

