



Powering Business Worldwide

pe.eaton.com

CX type current limiting fuse

4CXI-18C

UPC:786685407999

Dimensions:

- **Height:** X
- **Length:** 10 IN
- **Width:** X

Notes: Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CXI
- **Barrels:** Single barrel
- **Diameter:** 1.13 IN
- **Interrupt Rating:** 50 kA
- **Amperage Rating:** 18C
- **Class:** C
- **Maximum Voltage:** 4.3 kV
- **Nominal Voltage:** 2.4 kV

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Medium voltage power fuses](#)
- [Eaton Specification Sheet - 4CXI-18C](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data

