



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Safety Switch Body

LS-S11S

UPC:786685392486

### Dimensions:

- **Height:** 1.32 IN
- **Length:** 2.99 IN
- **Width:** 1.22 IN

Notes:0

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** Plus or minus 0.02mm
- **Connection:** Screw Terminals
- **Contact Rating:** 6A at 230 Vac, 3A at 24 Vdc
- **Contact Configuration:** 1NO-1NC with positive opening contact
- **Enclosure Material:** Plastic
- **Environmental Rating:** IP66, IP67
- **Maximum Ac Current:** 6A at 230 Vac
- **Maximum Dc Current:** 3A at 24 Vdc
- **Operating Speed:** 99.97 cm/sec
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** LS-Titan

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LS-S11S](#)

**Certifications:** No Data

**Product compliance:** No Data

