



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## LS-Titan Miniature DIN Limit Switch

LSM-20A

UPC:786685392158

### Dimensions:

- **Height:** 2.99 IN
- **Length:** 1.22 IN
- **Width:** 1.32 IN

**Weight:** .325 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:**  $\pm 0.02$ mm
- **Connection:** Cage Clamps
- **Contact Rating:** 6A at 240Vac, 3A at 24Vdc
- **Contact Configuration:** 2 NO, Slow Make Break
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** IP66, IP67
- **Maximum Ac Current:** 6A
- **Maximum Dc Current:** 3A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Top Push Plunger

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LSM-20A](#)

**Certifications:** No Data

**Product compliance:** No Data

