



Powering Business Worldwide

pe.eaton.com

LS-Titan Miniature DIN Limit Switch

LSM-11S

UPC:786685392134

Dimensions:

- **Height:** 2.99 IN
- **Length:** 1.22 IN
- **Width:** 1.32 IN

Weight: .325 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** ± 0.02 mm
- **Connection:** Cage Clamps
- **Contact Rating:** 6A at 240Vac, 3A at 24Vdc
- **Contact Configuration:** 1NO-1NC, Snap Action, Positive Opening
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** IP66, IP67
- **Maximum Ac Current:** 6A
- **Maximum Dc Current:** 3A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Top Push Plunger

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LSM-11S](#)

Certifications: No Data

Product compliance: No Data

