



Powering Business Worldwide

pe.eaton.com

LS-Titan Safety Interlock Switch

LSR-S11-1-I-TS

UPC:786685393889

Dimensions:

- **Height:** 3.5 IN
- **Length:** 1.18 IN
- **Width:** 2.24 IN

Weight: .1875 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 6A at 230Vac, 0.5A at 250Vdc
- **Contact Configuration:** 2NC, Slow Make Break, Positive Opening
- **Enclosure Material:** Polyamide PA66-GF25
- **Environmental Rating:** IP66, IP67
- **Maximum Ac Current:** 6A
- **Maximum Dc Current:** 3A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Cabinet Door Hinge Switch

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LSR-S11-1-I-TS](#)

Certifications: No Data

Product compliance: No Data

