



Powering Business Worldwide

pe.eaton.com

Interlock Switch

LS4-S11-1-I-ZB

UPC:786685393896

Dimensions:

- **Height:** 1.57 IN
- **Length:** 4.92 IN
- **Width:** 1.57 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 6A at 230 Vac, 3A at 24 Vdc
- **Mounting:** Full-size DIN
- **Contact Configuration:** 1NO-1NC with positive opening contact
- **Enclosure Material:** Plastic
- **Environmental Rating:** IP65
- **Maximum Ac Current:** 6A at 230 Vac
- **Maximum Dc Current:** 3A at 24 Vdc
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** LS-Titan
- **Switch Type:** Cabinet door interlock

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LS4-S11-1-I-ZB](#)

Certifications: No Data

Product compliance: No Data

