



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## LS-Titan Safety Interlock Switch

LS-S11-120AMT-ZBZ-X

UPC:786685393704

### Dimensions:

- **Height:** 6.81 IN
- **Length:** 2.36 IN
- **Width:** 1.21 IN

**Weight:** .95 LB

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 6A at 240Vac, 3A at 24Vdc
- **Contact Configuration:** 1NO-1NC, Slow Make Break, Positive Opening
- **Enclosure Material:** Polyamide PA66-GF25
- **Environmental Rating:** IP66, IP67
- **Input Voltage:** 120Vac
- **Maximum Ac Current:** 6A
- **Maximum Dc Current:** 3A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Cabinet Door Interlock

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LS-S11-120AMT-ZBZ-X](#)

**Certifications:** No Data

**Product compliance:** No Data

