



Powering Business Worldwide

pe.eaton.com

CurrentWatch Series Current Switch

ECSNCASC

UPC:786685120959

Dimensions:

- **Height:** 3.5 IN
- **Length:** 2.18 IN
- **Width:** .93 IN

Weight: .25 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 0.2A at 135 Vac/DC
- **Contact Configuration:** Isolated Solid State Relay
- **Enclosure Material:** UL94 V0 Flammability Rated Plastic
- **Led Indicators:** Red LED for contact status
- **Maximum Ac Current:** Monitor up to 150A, Switch up to 0.2A
- **Operating Temperature:** -58° to 122°F (-50° to 50°C)
- **Switch Type:** Current Switch

Supporting documents:

- [CurrentWatch current sensors](#)
- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - ECSNCASC](#)

Certifications: No Data

Product compliance: No Data

