



Powering Business Worldwide

pe.eaton.com

Enclosed Precision Limit Switch

E47BLS33D

UPC:782114111185

Dimensions:

- **Height:** 4 IN
- **Length:** 3.39 IN
- **Width:** 1 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 15A at 250 Vac, 6A at 30 Vdc
- **Accessories:** #6-32 screws
- **Actuator:** Booted roller lever
- **Contact Configuration:** 1-SPDT (Form C)
- **Enclosure Material:** Die cast aluminum
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 15A
- **Operating Speed:** 0.01 mm/s-1m/s
- **Operating Temperature:** -13° to 176°F (-25° to 80°C)
- **Series:** E47

Supporting documents:

- [E47 precision - Limit switches](#)
- [Eaton Specification Sheet - E47BLS33D](#)

Certifications: No Data

Product compliance: No Data

