



Powering Business Worldwide

pe.eaton.com

CE Marked Control Transformer

CE3000K6UCEFS

UPC:782116346752

Dimensions:

- **Height:** 8.268 IN
- **Length:** 6.575 IN
- **Width:** 9.016 IN

Weight:76.2 LB

Notes:Epoxy resin impregnated coil design, 50/60 Hz operation, 180°C insulation system

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Material:** Copper windings
- **Design:** MTK
- **Modification 1:** Factory-mounted finger-safe terminal shields
- **Primary Voltage:** 240/416/480/600V, 230/400/460/575V, 220/380/440/550V, 208/500V
- **Secondary Voltage:** 99/120/130V, 95/115/125V, 91/110/120V, 85/100/110V
- **Tap Size:** None
- **Temperature Rating:** 115°C
- **Type:** CE Marked Control Transformer
- **Volt Ampere Rating:** 3000 VA

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - CE3000K6UCEFS](#)

Certifications:



- UL Listed
- IEC 61558-2
- cUL Certified
- CSA Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.