



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 55 Series Photoelectric Sensor

1555R-6503

UPC:782114106693

### Dimensions:

- **Height:** 3.19 IN
- **Length:** 1.83 IN
- **Width:** 1.64 IN

**Weight:**.3375 LB

**Notes:**Glass fiber optic cables not included

### Warranties:

- 3 year

### Specifications:

- **Connection:** 5 Pin Mini Connector
- **Contact Rating:** 3A AC/DC at 120 Vac / 30 Vdc
- **Contact Configuration:** SPDT Form C Relay
- **Enclosure Material:** Body: Noryl, Lens: Nylon
- **Environmental Rating:** NEMA 1,3,4,6,12,13
- **Input Voltage:** 20–264 Vac 50/60 Hz or 15–30 Vdc (NPN)
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 3A
- **Operating Mode:** Fiberoptic
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 1555R-6503](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:



- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.