



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Prism Series Tubular Photoelectric Sensor

11155AA14

UPC:782113056524

### Dimensions:

- **Height:** 2.35 IN
- **Length:** .47 IN
- **Width:** .71 IN

**Weight:**.2875 LB

**Notes:**Synchronous design requires source and detector to be wired to each other

### Warranties:

- 3 year

### Specifications:

- **Connection:** 6.6 Ft. ( 2m ) Cable
- **Cable Type:** PVC
- **Cord Length:** 79.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: polycarbonate cable jacket: PVC body: structural polyurethane foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13
- **Input Voltage:** 20–132 Vac/15-30 Vdc
- **Led Indicators:** Red power on
- **Operating Mode:** Thru-beam
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 11155AA14](#)

### Certifications:

- UL Recognized



- cUL Recognized

**Product compliance:**

- CE Marked
- Contact Manufacturer

---

© 2016 Eaton. All rights reserved.