



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Prism Series Tubular Photoelectric Sensor

12155AL10

UPC:782113056562

### Dimensions:

- **Height:** 2.35 IN
- **Length:** .47 IN
- **Width:** .71 IN

**Weight:** .2875 LB

**Notes:** Synchronous design requires source and detector to be wired to each other

### Warranties:

- 3 year

### Specifications:

- **Connection:** 6.6 Ft. ( 2m ) Cable
- **Contact Rating:** 80 mA at 132 Vac / 110 mA at 132Vdc
- **Cable Type:** PVC
- **Contact Configuration:** Isolated Solid State Relay
- **Cord Length:** 79.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: polycarbonate cable jacket: PVC body: structural polyurethane foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 80 mA
- **Maximum Dc Current:** 110 mA
- **Operating Mode:** Thru-beam
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Current Limited for loads less than 32V AC or DC



- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

**Supporting documents:**

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 12155AL10](#)

**Certifications:**

- cUL Recognized
- UL Recognized

**Product compliance:**

- CE Marked
- Contact Manufacturer