



Powering Business Worldwide

pe.eaton.com

Series G, EG-frame Molded Case Circuit Breaker

EGH1030FFB

UPC:786685381718

Dimensions:

- **Height:** 5.5 IN
- **Length:** 2.99 IN
- **Width:** 1IN

Weight:1.5 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 30A
- **Interrupt Rating:** 100 kAIC at 240V, 70 kAIC at 415V, 65 kAIC at 480V, 35 kAIC at 600Y/347V
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 347V
- **Frame Size:** EG-frame
- **Series:** Series G
- **Terminals:** Bolt-on
- **Trip Type:** Fixed thermal, fixed magnetic

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - EGH1030FFB](#)

Certifications:

- IEC Rated
- CSA Certified
- UL Listed

Product compliance:



- CE Marked

© 2016 Eaton. All rights reserved.