



Powering Business Worldwide

pe.eaton.com

UL 1077 WMZS DIN Rail Supplementary Protector

WMZS3B40

UPC:786685259581

Dimensions:

- **Height:** 3.15 IN
- **Length:** 2.07 IN
- **Width:** 3.01 IN

Notes: Designed for Resistive or Slightly Inductive Loads

Warranties:

- 1 year

Specifications:

- **Type:** DIN rail mountable circuit breaker
- **Amperage Rating:** 40A
- **Interrupt Rating:** 10 kAIC at 277/480V
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 277/480V
- **Terminals:** Standard box terminals
- **Circuit Protection:** B Curve

Supporting documents:

- [Comprehensive Circuit protection for control panel applications](#)
- [Eaton's Volume 9-Original Equipment Manufacturer](#)
- [UL 1077 Supplementary Protectors](#)
- [UL1077 DIN Rail Mount WMZS 3 Pole](#)
- [Eaton Specification Sheet - WMZS3B40](#)

Certifications:

- UL 1077
- CSA Std. C22.2 No. 235
- IEC 60947-2

Product compliance:

- RoHS Compliant



- CE Marked

© 2016 Eaton. All rights reserved.