



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E58 Series Tubular Plastic Body Photoelectric Sensor

**E58CAL18T110C2**

**UPC:782113147512**

### Dimensions:

- **Height:** 2.2 IN
- **Length:** .47 IN
- **Width:** .71 IN

**Weight:**.2875 LB

**Notes:**Short circuit and reverse polarity protected.  
For complete system; order 1 source and 1 detector.

### Warranties:

- 3 year

### Specifications:

- **Connection:** 9.8 Ft. ( 3m ) Cable
- **Contact Rating:** NPN: 250 mA at 30Vdc
- **Cable Type:** PVC
- **Contact Configuration:** NPN Open Collector
- **Cord Length:** 120 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 12 and 13, IP69k
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red Output Status
- **Maximum Dc Current:** 250 mA
- **Operating Mode:** Thru-Beam
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset short circuit
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

**Supporting documents:**



- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E58CAL18T110C2](#)

**Certifications:** No Data

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.