



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 3/4 in Type CH EUCERC Retrofit Meter Breaker

**CMBE24B100TFR**

**UPC:**786685361703

### Dimensions:

- **Height:** 6.5 IN
- **Length:** 34.5 IN
- **Width:** 14.7 IN

**Weight:**45 LB

### Warranties:

- Limited lifetime

### Specifications:

- **Type:** Retrofit solutions
- **Amperage Rating:** 100A
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Overhead
- **Interrupt Rating:** 35 kAIC
- **Main Circuit Breaker:** CSR2100BM
- **Mounting:** Flush mounting
- **Number Of Circuits:** 4
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Number Of Spaces:** 2
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type CH breakers
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eaton Specification Sheet - CMBE24B100TFR](#)

### Certifications:

- UL Listed

### Product compliance:



- EUSERC Approved

---

© 2016 Eaton. All rights reserved.