



Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor

13150RD07

UPC:782113976013

Dimensions:

- **Height:** .71 IN
- **Length:** 2.6 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Connection:** M12
- **Contact Rating:** 80 mA AC/100 mA DC at 20-132V
- **Contact Configuration:** Isolated SSR
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 2, 3, 4, 4X, 6, 12, 13
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 80 mA
- **Maximum Dc Current:** 100 mA
- **Number Of Pins:** 4 pin
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** Protected for loads < 32 Vac or 2 Vdc
- **Sensor Type:** Diffuse Reflective

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 13150RD07](#)

Certifications:

- cUL Recognized
- UL Recognized

Product compliance: No Data



