



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Thermal-Magnetic Circuit Breaker

BAB2020D

UPC:786679153178

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.8 IN
- **Width:** 2.2 IN

Weight:.65 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Special Features:** High Intensity Discharge
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Circuit Breaker Type:** BAB
- **Trip Type:** Non-Interchangeable
- **Mounting:** Bolt-on
- **Quantity:** 12

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB2020D](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data



