



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Type PS Precision Limit Switch

10316H2042

UPC:782113257945

### Dimensions:

- **Height:** 3.19 IN
- **Length:** 1.03 IN
- **Width:** 2.6 IN

**Weight:**.3125 LB

**Notes:**The plunger when pulled out exposes a red band to indicate that the interlock is defeated

### Warranties:

- 1 year

### Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 30A MK, 3A BK at 120 Vac, 0.2A MK/BK at 120 Vdc
- **Contact Configuration:** 2NO-2NC
- **Enclosure Material:** Zinc Plated Steel
- **Maximum Ac Current:** 30A Make, 3A Break
- **Maximum Dc Current:** 0.2A Make, 0.2A Break
- **Switch Type:** Cabinet Door Interlock

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H2042](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- Contact Manufacturer

