



Powering Business Worldwide

pe.eaton.com

E47 Enclosed Precision Limit Switch

E47CLS06

UPC:782116062171

Dimensions:

- **Height:** 3.39 IN
- **Length:** 1 IN
- **Width:** 2.8 IN

Weight:.5125 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 20A at 125Vac / 20A at 14Vdc
- **Contact Configuration:** SPDT
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 20A
- **Operating Temperature:** 5° to 176°F (-15° to 80°C)
- **Switch Type:** Booted Plunger

Supporting documents:

- [E47 precision - Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47CLS06](#)

Certifications: No Data

Product compliance: No Data

