



Powering Business Worldwide

pe.eaton.com

CurrentWatch Series Current Transducer

EACR2420SC

UPC:786685120706

Dimensions:

- **Height:** 3.5 IN
- **Length:** 2.18 IN
- **Width:** .93 IN

Weight:.25 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** 1% FS
- **Connection:** Screw Terminals
- **Enclosure Material:** UL94 V0 Flammability Rated Plastic
- **Input Voltage:** 24Vdc Current Loop
- **Led Indicators:** No
- **Maximum Ac Current:** Measure up to 200A
- **Operating Temperature:** -4° to 122°F (-20° to 50°C)
- **Switch Type:** Current Sensor

Supporting documents:

- [CurrentWatch current sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - EACR2420SC](#)

Certifications: No Data

Product compliance: No Data

