



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Photoelectric Sensor

**E71-PRP-M8**

**UPC:**786685262208

### Dimensions:

- **Height:** 1.41 IN
- **Length:** .79 IN
- **Width:** .47 IN

### Warranties:

- 3 year

### Specifications:

- **Connection:** M8
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Contact Configuration:** Complementary PNP open collector
- **Enclosure Material:** ABS UL 94V-0
- **Environmental Rating:** IP66
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output (yellow), stability (green), power (green)
- **Maximum Dc Current:** 100 mA
- **Number Of Pins:** 4 pin
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Protection:** S/C and reverse polarity
- **Sensor Type:** Polarized Retroreflective
- **Series:** E71

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Introducing NanoView Series sensors](#)
- [Eaton Specification Sheet - E71-PRP-M8](#)

**Certifications:** No Data

**Product compliance:** No Data



