



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Series C, N-frame Molded Case Mining Circuit Breaker

**E2N3800W**

**UPC:**786679060001

### Dimensions:

- **Height:** 16 IN
- **Length:** 5.5 IN
- **Width:** 8.25 IN

**Weight:**45 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Specialty complete
- **Amperage Rating:** 800A
- **Interrupt Rating:** 65 kAIC at 240V, 50 kAIC at 480V, 25 kAIC at 600V
- **Number Of Poles:** Three-pole
- **Frame Size:** N-frame
- **Magnetic Trip Range:** 500-2500A
- **Maximum Voltage:** 600V
- **Series:** Series C
- **Trip Type:** LI electronic

### Supporting documents:

- [E2 Mining Series Sales Brochure](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - E2N3800W](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data



