



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Series C, Molded Case Circuit Breaker

**E2K3300W**

**UPC:**782114110959

### Dimensions:

- **Height:** 10.13 IN
- **Length:** 4.1 IN
- **Width:** 5.5 IN

**Weight:**11.5 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Specialty complete
- **Amperage Rating:** 300A
- **Interrupt Rating:** 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, 25 kAIC at 600 Vac, 10 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Trip Type:** Fixed thermal, fixed magnetic
- **Trip Setting Amperage:** 1500-3000A
- **Circuit Breaker Type:** E2
- **Class:** Mining
- **Frame Size:** K-frame
- **Maximum Voltage:** 600V
- **Series:** Series C
- **Terminals:** Without terminals
- **Trip Type:** Interchangeable thermal-magnetic

### Supporting documents:

- [E2 Mining Series Sales Brochure](#)
- [Eatons Volume 4-Circuit Protection](#)



- [Eaton Specification Sheet - E2K3300W](#)

**Certifications:**

- CSA Certified
- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.