



Powering Business Worldwide

pe.eaton.com

Power Supply

EAC2420SP

UPC:786685120607

Dimensions:

- **Height:** 2.25 IN
- **Length:** 3.3 IN
- **Width:** 1.2 IN

Warranties:

- 1 year

Specifications:

- **Accuracy:** 1.0% FS
- **Connection:** Screw Terminals
- **Enclosure:** Split-Core housing
- **Contact Configuration:** 4-20mA analog output
- **Enclosure Material:** UL94 V0 flammability rated plastic
- **Input Voltage:** 24 Vdc loop powered
- **Maximum Ac Current:** 200A
- **Operating Temperature:** -4° to 122°F (-20° to 50°C)
- **Used With:** Used with CurrentWatch EAC Top Terminal Current Sensor

Supporting documents:

- [CurrentWatch current sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - EAC2420SP](#)

Certifications: No Data

Product compliance: No Data

