



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## Spring Cage Connection Multi-Conductor Terminal Blocks

**XBPT25D12**

**UPC:**782116905584

### Dimensions:

- **Height:** 2.38 IN
- **Length:** .2 IN
- **Width:** X

### Warranties:

- 1 year

### Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** IEC 28A, EN 25,21A, UL 20A
- **Color:** Gray
- **Maximum Wire Size:** 12 AWG/2.5 mm<sup>2</sup>
- **Number Of Wires:** Three-wire
- **Voltage Rating:** IEC 800V, EN 550V, UL 600V
- **Wire Size:** IEC #28-12 AWG, EN #24-12, UL #26-12 AWG

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC TERMINAL BLOCKS](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBPT25D12](#)

### Certifications:

- CSA Certified
- UL Listed

**Product compliance:** No Data

---

