



Powering Business Worldwide

pe.eaton.com



Spring Cage Connection Multi-Conductor Ground Blocks

XBPT4D12

UPC:782116905614

Dimensions:

- **Height:** 2.81 IN
- **Length:** .24 IN
- **Width:** X

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** IEC 40A, EN 34A, UL 30A
- **Color:** Gray
- **Maximum Wire Size:** 10 AWG/4 mm²
- **Voltage Rating:** IEC 800V, EN 550V, UL 600V
- **Wire Size:** IEC #28-10 AWG, EN #24-10 AWG, UL #20-10 AWG

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC TERMINAL BLOCKS](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBPT4D12](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data