



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Rotary Disconnects

**ER53040UG**

**UPC:**786685465999

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 40A
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Max Hp Rating:** 7.5 at 208 Vac, 7.5 at 240 Vac, 20 at 480 Vac, 25 at 600 Vac
- **Number Of Poles:** Three-pole
- **Product Category:** Enclosed Rotary Non-Fusible
- **Series:** R-Series
- **Voltage Rating:** 600V

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - ER53040UG](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data

