



Powering Business Worldwide

pe.eaton.com

E57 Global Series Tubular Inductive Proximity Sensor

E57-12GE10-CDB

UPC:786685125312

Dimensions:

- **Height:** 2.7 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight:.0625 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 100 mA at 30 Vdc
- **Contact Configuration:** NPN Open Collector, Normally Open
- **Diameter:** .47 IN
- **Enclosure Material:** Nickel Plated Brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-12GE10-CDB](#)

Certifications: No Data



Product compliance: No Data

© 2016 Eaton. All rights reserved.