



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Dry Type Distribution Ventilated Transformer

**T24M11S05**

**UPC:**786680104121

### Dimensions:

- **Height:** 30.25 IN
- **Length:** 15.82 IN
- **Width:** 16.87 IN

**Weight:**162 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Dry type distribution, ventilated transformer
- **Design:** DS-3
- **Coil Material:** Aluminum windings
- **Enclosure:** NEMA 2
- **Frame:** 815
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 240V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 5 KVA
- **Weathershield:** WS15
- **Wiring Connection:** 262P

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - T24M11S05](#)

### Certifications:



- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.