



Powering Business Worldwide

pe.eaton.com

E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor Head

E51DP9

UPC:782113645964

Dimensions:

- **Height:** 1.77 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

Weight:.1625 LB

Warranties:

- 3 year

Specifications:

- **Enclosure Material:** Plastic
- **Environmental Rating:** NEMA 3,3S,4,4X,6,6P,12,13, IP67
- **Operating Mode:** Polarized Retroreflective
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Photoelectric

Supporting documents:

- [Eaton Specification Sheet - E51DP9](#)

Certifications: No Data

Product compliance: No Data

