



Powering Business Worldwide

pe.eaton.com

E57 Small Diameter Series Inductive Proximity Sensor



E57-08GU02-GNB

UPC:782114664957

Dimensions:

- **Height:** 2.36 IN
- **Length:** .31 IN
- **Width:** .31 IN

Weight:.05 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 3 Pin M8 Connector
- **Contact Rating:** 100 mA at 30 Vdc
- **Contact Configuration:** PNP Open Collector, Normally Open
- **Diameter:** .315 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** 32° to 140°F (0° to 60°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-08GU02-GNB](#)

Certifications: No Data

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.