



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Tubular Sensor

E55CAL18T111

UPC:782113888224

Dimensions:

- **Height:** .71 IN
- **Length:** 2.17 IN
- **Width:** .71 IN

Warranties:

- 1 year

Specifications:

- **Type:** Inductive Proximity Tubular Sensor
- **Contact Rating:** 200 mA
- **Cable Type:** PVC
- **Contact Configuration:** NO PNP open collector
- **Cord Length:** 79.2 FT
- **Diameter:** .708661422 MM
- **Enclosure Material:** PBT
- **Environmental Rating:** NEMA 3, 3S, 4, 4X, 13, IP66
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Number Of Wires:** 3-wire
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** S/C and reverse polarity
- **Series:** E55

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E55CAL18T111](#)

Certifications: No Data

Product compliance: No Data



