



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## General-Purpose Transformer

**V60M28T12EE**

**UPC:**786680052309

**Dimensions:**

- **Height:** 48.56 IN
- **Length:** 23.42 IN
- **Width:** 28.22 IN

**Weight:**801 LB

**Notes:**NEMA TP-1 efficient

**Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Specifications:**

- **Type:** Dry Type Distribution Transformer
- **Design:** DT-3
- **Coil Material:** Aluminum windings
- **Frame:** 916A
- **Frequency Rating:** 60 Hz
- **Phase:** Three-phase
- **Primary Voltage:** 600V
- **Secondary Voltage:** 208Y/120V
- **Tap Size:** 2 at +2.5% FCAN, 4 at -2.5% FCBN
- **Temperature Rating:** 150°C
- **Volt Ampere Rating:** 112.5 KVA
- **Weathershield:** WS19

**Supporting documents:**

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - V60M28T12EE](#)

**Certifications:**

- UL Listed

**Product compliance:**



- NEMA TP-1 Compliant

---

© 2016 Eaton. All rights reserved.