



Powering Business Worldwide

pe.eaton.com

E57 Premium+ Series Tubular Inductive Proximity Sensor

E57LBL12T111SD

UPC:782113605012

Dimensions:

- **Height:** 2.71 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight: .0625 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 500 mA at 6-30Vdc
- **Contact Configuration:** Normally Closed PNP
Open Collector
- **Diameter:** .47 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** IP67, IP69K, UL Type
1, NEMA 6P, 4X
- **Input Voltage:** 6–48 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 500 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to
70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LBL12T111SD](#)

Certifications:

- CSA Certified



- UL Listed

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.