



Powering Business Worldwide

pe.eaton.com

LS-Titan Miniature DIN Limit Switch

LSM-02-S

UPC:786685392325

Dimensions:

- **Height:** 4.96 IN
- **Length:** 1.22 IN
- **Width:** 1.32 IN

Weight:.325 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Cage Clamps
- **Contact Rating:** 6A at 240Vac, 3A at 24Vdc
- **Contact Configuration:** 2NC, Slow Make Break, Positive Opening
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** IP66, IP67
- **Maximum Ac Current:** 6A
- **Maximum Dc Current:** 3A
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Wobble Stick, Spring Rod

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [LS-Titan Safety Limit Switches](#)
- [Eaton Specification Sheet - LSM-02-S](#)

Certifications: No Data

Product compliance: No Data

