



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Heavy Duty Safety Switch

DH421FDK

UPC:782113205458

### Dimensions:

- **Height:** 9 IN
- **Length:** 25.5 IN
- **Width:** 13.25 IN

**Weight:**40 LB

**Notes:**Can be field modified to meet NEMA 3R rainproof requirements when a factory provided drain hole is opened

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible without neutral
- **Number Of Poles:** Four-pole
- **Number Of Wires:** Four-wire
- **Product Category:** Heavy Duty, Fusible without neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 0.5 at 240 Vac Std. 1 Ph, 3 at 240 Vac Std. 3 Ph, 3 at 240 Vac TD 1 Ph, 7.5 at 240 Vac TD 3 Ph, 5 at 250 Vdc

### Supporting documents:

- [Eaton's Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH421FDK](#)



**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.