



Powering Business Worldwide

pe.eaton.com

E57 Series Tubular Ferrous Only Inductive Proximity Sensor

E57FAL18T111SD

UPC:782113884714

Dimensions:

- **Height:** 3.11 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight:.1438 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 100 mA at 30 Vdc
- **Contact Configuration:** Normally Open PNP
Open Collector
- **Diameter:** .71 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12
and 13 (IP67)
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to
70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57FAL18T111SD](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.