



Powering Business Worldwide

pe.eaton.com

E57 Premium+ Series Short Body Tubular Inductive Proximity Sensor

E57SBL18A2EA

UPC:782113698847

Dimensions:

- **Height:** 2.72 IN
- **Length:** .71 IN
- **Width:** .71 IN

Weight: .14 LB

Notes: Contact factory for current series transition. Cable models are supplied as standard with a 2-meter cable. A 5-meter cable is available by adding S5 to the catalog number. Example: E57SALT110 becomes E57SALT110S5.

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 3%
- **Connection:** 3 Pin Dual Key Micro Connector
- **Contact Rating:** 250 mA at 40-240Vac/20-250Vdc
- **Contact Configuration:** 2 - Wire AC/DC, Normally Closed
- **Diameter:** .71 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 40–250 Vac /20–250 Vdc
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 250 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)



- **Protection:** None
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57SBL18A2EA](#)

Certifications: No Data

Product compliance: No Data