



Powering Business Worldwide

pe.eaton.com

CurrentWatch Series Ground Fault Sensor

EGF1NCLAT3

UPC:786685120881

Dimensions:

- **Height:** 3.88 IN
- **Length:** 1.5 IN
- **Width:** 2.5 IN

Weight: .25 LB

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 1A at 240Vac
- **Contact Configuration:** Isolated Solid State Relay
- **Enclosure Material:** UL94 V0 Flammability Rated Plastic
- **Input Voltage:** 120Vac
- **Led Indicators:** Green LED for power ON status red LED for contact status
- **Maximum Ac Current:** 1A
- **Operating Temperature:** -4° to 122°F (-20° to 50°C)
- **Switch Type:** Current Switch

Supporting documents:

- [CurrentWatch current sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - EGF1NCLAT3](#)

Certifications: No Data

Product compliance: No Data



