



Powering Business Worldwide

pe.eaton.com

50 Series Photoelectric Sensor

1550B-6501

UPC:782113825595

Dimensions:

- **Height:** 3.19 IN
- **Length:** 1.64 IN
- **Width:** 1.83 IN

Weight: .2625 LB

Notes: Glass fiber optic cables not included

Warranties:

- 3 year

Specifications:

- **Connection:** 5 Pin Mini Connector
- **Contact Rating:** Depends on Output Device
- **Enclosure Material:** Body: Noryl, Lens: Nylon
- **Environmental Rating:** NEMA 1,3,4,12,13
- **Input Voltage:** 90-132 Vac
- **Led Indicators:** Red output status
- **Operating Mode:** Fiberoptic, Infrared
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Sensor Type:** Fiberoptic
- **Switch Type:** Photoelectric

Supporting documents:

- [Eaton Specification Sheet - 1550B-6501](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- Contact Manufacturer

