



Powering Business Worldwide

pe.eaton.com

CLE Helix type current limiting fuse

5CLE-600E

UPC:786670219514

Dimensions:

- **Height:** X
- **Length:** 10.87 IN
- **Width:** X

Notes:Consult factory for mountings.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** CLE
- **Application:** Indoor
- **Barrels:** Double barrel
- **Clip Center:** 14
- **Diameter:** 5.31 IN
- **Interrupt Rating:** 40 kA
- **Mounting:** Bolt-in
- **Amperage Rating:** 600A
- **Class:** E
- **Maximum Voltage:** 5.5 kV
- **Nominal Voltage:** 4.8 kV

Supporting documents:

- [Eatons Volume 14-Fuses](#)
- [Medium voltage power fuses](#)
- [Eaton Specification Sheet - 5CLE-600E](#)

Certifications:

- IEEE Std. C37.41

Product compliance: No Data



