



Powering Business Worldwide

pe.eaton.com

Solar DC Disconnect

DCG3061UPM

UPC:786685556765

Dimensions:

- **Height:** 19.08 IN
- **Length:** 10.22 IN
- **Width:** 8.76 IN

Weight:21 LB

Notes:Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** DC disconnect/grounded system
- **Amperage Rating:** 30A
- **Enclosure:** NEMA 4
- **Enclosure Material:** Painted steel
- **Fuse Configuration:** Non-fusible
- **Ground:** Grounded
- **Main Lug Wire Size:** #14-#2 AWG lug capacity, #14-1/0 AWG solid return
- **Number Of Circuits:** 3 circuits
- **Series:** DC Photovoltaic Applications
- **Voltage Rating:** 600 Vdc
- **Wire Size:** #14-#4 AWG input grd., #14-#4 AWG output grd.

Supporting documents:

- [DC disconnects for grounded and ungrounded photovoltaic installations](#)



- [Eatons Volume 15-Solar Inverters and Electrical Balance of System](#)
- [Eaton Specification Sheet - DCG3061UPM](#)

Certifications:

- UL 98B
- NEC 690 per UL 1741

Product compliance: No Data

© 2016 Eaton. All rights reserved.