



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Heavy Duty Safety Switch

DH226NWK

UPC:782114371220

### Dimensions:

- **Height:** 63 IN
- **Length:** 12.84 IN
- **Width:** 23 IN

**Notes:**3-Phase hp ratings shown are grounded B phase ratings; UL listed

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 600A
- **Enclosure:** NEMA 4X
- **Enclosure Material:** Stainless steel
- **Fuse Class Provision:** Class H fuses
- **Fuse Configuration:** Fusible with neutral
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Fusible with neutral
- **Voltage Rating:** 240V
- **Max Hp Rating:** 75 at 240 Vac Std. 3 Ph, 200 at 240 Vac TD 3 Ph

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - DH226NWK](#)

### Certifications:

- UL Listed

**Product compliance:** No Data



