



Powering Business Worldwide

pe.eaton.com

E47BCC Series Compact Pre-Wired Limit Switch

E47BCC22

UPC:786685345857

Dimensions:

- **Height:** 3.6 IN
- **Length:** 1.58 IN
- **Width:** 2.16 IN

Weight:1.0438 LB

Warranties:

- 1 year

Specifications:

- **Connection:** 10 Ft. (3m) Cable
- **Contact Rating:** 5A at 240 Vac/5A at 14 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** SPDT
- **Cord Length:** 120 FT
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 4, 6 and 13 IEC IP67
- **Maximum Ac Current:** 5A
- **Operating Temperature:** 14° to 158°F (-10° to 70°C)
- **Switch Type:** Adjustable Side Rotary

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47BCC22](#)

Certifications: No Data

Product compliance: No Data

